Super Series Slit Lamp Lenses



Available in 7 different colors

Super 66®

Primary Application - High Magnification Viewing of the Central Retina

- Enables 3D discernment of subtle macular and optic disc detail
- 1.0x magnification simplifies optic disc measurement

Product code: VS66



2D View

2D View



Field of View




Available in 7 different colors

Super Field NC®

Primary Application - Wide Field, Pan Retinal Examination

- · 'Super 90D'. Same magnification with a wider field of view
- Highly versatile lens with multiple contact and non contact options
- · Increased working distance compared to competitive fundus lenses





Field of View



Super VitreoFundus®

Primary Application – Wide Field, Pan Retinal Examination and Small Pupil Capability

- Widest field of view in a non contact lens with views past the vortex
- Excellent small pupil capability through a 3 4mm pupil



Field of View 103" / 124"


Field of View




Super Pupil® XL

Primary Application – Small Pupil Pan Retinal Examination

- Optimal small pupil capability through a pupil as small as 2 3mm
- · Excellent for diabetic patients with miotic eyes





Field of View